




ES SERIES 2-WAY VALVES

ES-2S -



Normally Closed 2-Way Electronic Poppet Valve with Side Pin Connectors



Input Pressure: 28" Hg Vac. to 105 psig
28" Hg Vac. to 50 psig (L)
25" Hg Vac. to 50 psig (H)


Air Flow: 0.6 scfm @ 100 psig
0.5 scfm @ 50 psig (L)
0.45 scfm @ 25 psig (H)

Ports: Inlet and outlet through manifold

ES-2T -



Normally Closed 2-Way Electronic Poppet Valve with Top Pin Connectors



Input Pressure: 28" Hg Vac. to 105 psig
28" Hg Vac. to 50 psig (L)
25" Hg Vac. to 50 psig (H)


Air Flow: 0.6 scfm @ 100 psig
0.5 scfm @ 50 psig (L)
0.45 scfm @ 25 psig (H)

Ports: Inlet and outlet through manifold

ES-2W -



Normally Closed 2-Way Electronic Poppet Valve with Wire Leads



Input Pressure: 28" Hg Vac. to 105 psig
28" Hg Vac. to 50 psig (L)
25" Hg Vac. to 50 psig (H)


Air Flow: 0.6 scfm @ 100 psig
0.5 scfm @ 50 psig (L)
0.45 scfm @ 25 psig (H)

Ports: Inlet and outlet through manifold

ES-2B -



Normally Closed 2-Way Electronic Poppet Valve with Board Mount



Input Pressure: 28" Hg Vac. to 105 psig
28" Hg Vac. to 50 psig (L)
25" Hg Vac. to 50 psig (H)

Air Flow: 0.6 scfm @ 100 psig
0.5 scfm @ 50 psig (L)
0.45 scfm @ 25 psig (H)

Ports: Inlet and outlet through manifold

For Cable and Connectors, see Page 184.