


ES SERIES 3-WAY VALVES



ES-3S -



Normally Closed 3-Way Electronic Poppet Valve with Side Pin Connector



Input Pressure: 28" Hg Vac. to 105 psig
28" Hg Vac. to 50 psig (L)
25" Hg Vac. to 50 psig (H)


Air Flow: 0.6 scfm @ 100 psig
0.5 scfm @ 50 psig (L)
0.45 scfm @ 25 psig (H)

Ports: Inlet and outlet through manifold;
3-way exhaust through top of valve

ES-3T -



Normally Closed 3-Way Electronic Poppet Valve with Top Pin Connector



Input Pressure: 28" Hg Vac. to 105 psig
28" Hg Vac. to 50 psig (L)
25" Hg Vac. to 50 psig (H)


Air Flow: 0.6 scfm @ 100 psig
0.5 scfm @ 50 psig (L)
0.45 scfm @ 25 psig (H)

Ports: Inlet and outlet through manifold;
3-way exhaust through top of valve

ES-3W -



Normally Closed 3-Way Electronic Poppet Valve with Wire Leads



Input Pressure: 28" Hg Vac. to 105 psig
28" Hg Vac. to 50 psig (L)
25" Hg Vac. to 50 psig (H)


Air Flow: 0.6 scfm @ 100 psig
0.5 scfm @ 50 psig (L)
0.45 scfm @ 25 psig (H)

Ports: Inlet and outlet through manifold;
3-way exhaust through top of valve

ES-3B -



Normally Closed 3-Way Electronic Poppet Valve with Board Mount



Input Pressure: 28" Hg Vac. to 105 psig
28" Hg Vac. to 50 psig (L)
25" Hg Vac. to 50 psig (H)

Air Flow: 0.6 scfm @ 100 psig
0.5 scfm @ 50 psig (L)
0.45 scfm @ 25 psig (H)

Ports: Inlet and outlet through manifold;
3-way exhaust through top of valve

For Cable and Connectors, see Page 184.