

## MQC-2S

**NEW!** Quick Connect Assembly

**Type:** One way check quick connect assembly of valve body MQC-V2 and hose connector MQC-F


**Material:** Body- brass, Stem- brass

**Seals:** Buna-N

**Working Pressure:** 0 to 300 psig

**Air Flow:** 3.0 scfm @ 50 psig  
5.8 scfm @ 100 psig

**Triple Barb:** Order #MQC-2



## MQC-3S

**NEW!** Quick Connect Assembly

**Type:** One way check quick connect assembly of valve body MQC-V3 and hose connector MQC-F


**Material:** Body- brass, Stem- brass

**Seals:** Buna-N

**Working Pressure:** 0 to 300 psig

**Air Flow:** 3.0 scfm @ 50 psig  
5.8 scfm @ 100 psig

**Triple Barb:** Order #MQC-3 or MQC-3-M5 (metric)



## MQC-V2

Valve Body

**Material:** Brass


**Thread:** #10-32 male

**Mounting:** In panel or bracket to 1/4" thick with two 7/16" mounting nuts and lockwashers furnished; like screws directly into operative unit or manifold

**Seals:** Buna-N

**Use:** For connection with external shut-off to external hose, use hose connectors: MQC-F, MQC-FT, MQC-F2

**Options:** (-NP)



## MQC-V3

Valve Body

**Material:** Brass


**Thread:** Tapped #10-32

**Mounting:** In panel or bracket to 1/4" thick with two 7/16" mounting nuts and lockwashers furnished; like MQC-V2, but end is tapped #10-32 instead of threaded

**Seals:** Buna-N

**Use:** For connection with external shut-off to external hose, use hose connectors: MQC-F, MQC-FT, MQC-F2

**Options:** (-NP), (-M5)



## MQC-VP

Valve Body

**Material:** Brass

**Thread:** 1/8" NPT base; 5/16-24 body

**Use:** For connection with external shut-off to external hose, use hose connectors: MQC-F, MQC-FT, MQC-F2

**Seals:** Buna-N

**Options:** (-NP), (-MR), (-MG)

