# **4-WAY FULLY-PORTED STEM VALVES**






4-WAY FULLY-PORTED STEM VALVES 4-way fully-ported valves have

outlets and one exhaust port. When the stem is in one position air flows from one inlet to its outlet while the other inlet is blocked. Moving the stem to the opposite position reverses this action. This may be defined as two 3-way valves, one Normally Closed and one Normally Open operating simultaneously. 4-way fully ported stem valves may either be spring return or double acting. A double acting stem must be moved from one position to the other, a spring return stem will move to the opposite position when released.

4-Way Fully-Ported Valves

# 4-Way Fully-Ported Valves





Medium: Air or Oil

Air Flow: 6.0 SCFM @ 50 psig; 10 SCFM @ 100 psig; 240 l/min @ 6 bar



F


Force For Full Stem Travel: FV-5 & FV-5-M5 - 4 1/2 lb. nominal; FV-5D & FV-5D-M5 - 1 1/2 lb. nominal

#### Part No. Description EV-5 ...... Plunger Actuated Spring Return Valve, #10-32


FV-5-M5 Plunger Actuated Spring Return Valve, M5	
FV-5D 2 Position Double Plunger Valve, #10-32	
FV-5D-M5 . 2 Position Double Plunger Valve, M5	

## Flow Paths for "FTV & FV" Series

Solid lines indicate flow paths with toggle or stem in one direction. Dotted lines indicate flow paths when the toggle or stem are shifted.



#### 0.625 1 250 15.9) (31.8)



### Medium: Air or Oil

Air Flow: 6.5 SCFM @ 50 psig; 10.5 SCFM @ 100 psig; 250 l/min @ 6 bar



Force For Full Stem Travel: FV-5P & FV-5-MG - 4 1/2 lb. nominal; FV-5DP & FV-5D-MG - 1 1/2 lb. nominal

Part No. Description FV-5P ..... Plunger Actuated Spring Return Valve, 1/8" NPT FV-5-MG . . . . Plunger Actuated Spring Return Valve, G1/8

FV-5DP	2 Position	Double	Plunger	Valve,	1/8" NPT	
FV-5D-MG	2 Position	Double	Plunger	Valve,	G1/8	

Clippard Instrument Laboratory, Inc. 877-245-6247 www.clippard.com