




# ES SERIES 2- & 3-WAY VALVES

Normally Closed 2 & 3-Way Electronic Poppet Valves with Side Pin Connector



**Input Pressure:** 28" Hg Vac. to 105 psig  
28" Hg Vac. to 50 psig (L)  
25" Hg Vac. to 50 psig (H)


**Air Flow:** 0.6 scfm @ 100 psig  
0.5 scfm @ 50 psig (L)  
0.45 scfm @ 25 psig (H)

**Ports:** Inlet and outlet through manifold;  
3-way exhaust through top of valve (3-way only)

**Order No.**

- ES-2S-□ 2-Way Electronic Poppet Valve
- ES-3S-□ 3-Way Electronic Poppet Valve

Normally Closed 2- & 3-Way Electronic Poppet Valves with Top Pin Connector



**Input Pressure:** 28" Hg Vac. to 105 psig  
28" Hg Vac. to 50 psig (L)  
25" Hg Vac. to 50 psig (H)


**Air Flow:** 0.6 scfm @ 100 psig  
0.5 scfm @ 50 psig (L)  
0.45 scfm @ 25 psig (H)

**Ports:** Inlet and outlet through manifold;  
3-way exhaust through top of valve (3-way only)

**Order No.**

- ES-2T-□ 2-Way Electronic Poppet Valve
- ES-3T-□ 3-Way Electronic Poppet Valve

Normally Closed 2- & 3-Way Electronic Poppet Valves with Wire Leads



**Input Pressure:** 28" Hg Vac. to 105 psig  
28" Hg Vac. to 50 psig (L)  
25" Hg Vac. to 50 psig (H)


**Air Flow:** 0.6 scfm @ 100 psig  
0.5 scfm @ 50 psig (L)  
0.45 scfm @ 25 psig (H)

**Ports:** Inlet and outlet through manifold;  
3-way exhaust through top of valve (3-way only)

**Order No.**

- ES-2W-□ 2-Way Electronic Poppet Valve
- ES-3W-□ 3-Way Electronic Poppet Valve

Normally Closed 2- & 3-Way Electronic Poppet Valves with Board Mount



**Input Pressure:** 28" Hg Vac. to 105 psig  
28" Hg Vac. to 50 psig (L)  
25" Hg Vac. to 50 psig (H)

**Air Flow:** 0.6 scfm @ 100 psig  
0.5 scfm @ 50 psig (L)  
0.45 scfm @ 25 psig (H)

**Ports:** Inlet and outlet through manifold;  
3-way exhaust through top of valve (3-way only)

**Order No.**

- ES-2B-□ 2-Way Electronic Poppet Valve
- ES-3B-□ 3-Way Electronic Poppet Valve

For Cable and Connectors, see Page 215.