## THE MOUSE VALVE SERIES



## **Clippard Functional Simplicity**

- The design of Clippard electronic valves is a deceptively simple arrangement with a minimum of operating parts, and remarkably straight forward low power operation.
- The Clippard "spider" is the only moving part and its motion to operate the valve is a mere 0.007" travel.
- Low voltage D.C. inputs, signals from simple manual switching up to computer directed systems, move the spider in extremely fast response time . . . 5 to 10 milliseconds.
- The unit uses extremely low power (0.67 watts at the rated voltage) and is cool running. The valves are light in weight, compact in physical size and mount easily in space-saving packages.


## **Quick Connect**

Clippard ET valves feature spade lugs for simple, quick secure low voltage connections. Wire crimp-on spade lug connectors are available separately to adapt electronic wiring where necessary. Clippard original EV type



valves are available in popular voltages with 18" wire leads. The EC model utilizes a 0.025" square pin connector. Easy Mounting

The complete line of EC, EV, ET and EW electronic valves are available with two mounting options. Standard base models have two 6-32



threaded, 7/32" deep mounting holes. Manifold models are equipped with a bottom stud, 5/32" long with #10-32 thread, which fits Clippard standard and special manifolds, accessory valves and subplates. Spanner holes in the valve body permit tightening.

NOMINAL					Working Range
Series	Voltage	Current (amps)	Resistance (ohms)	Power (watts)	(cont. duty)
Standard	6	0.11	54	0.67	90 to 150% of rated voltage
Oxygen Clean	12	0.055	218	0.67	
Scientific	24	0.028	864	0.67	
Corrosion-	12	0.098	122	1.2	90 to 110%
Resistant	24	0.049	486	1.2	of rated voltage