


ES SERIES 2- & 3-WAY VALVES



Normally-Closed 2 & 3-Way Electronic Poppet Valves with Side Pin Connector




Part No.	Description
ES-2S-□	2-Way Electronic Poppet Valve
ES-3S-□	3-Way Electronic Poppet Valve

Input Pressure: 28" Hg Vac. to 105 psig
 28" Hg Vac. to 50 psig (L)
 28" Hg Vac. to 25 psig (H)

Air Flow: 0.6 scfm @ 100 psig
 0.5 scfm @ 50 psig (L)
 0.45 scfm @ 25 psig (H)

Ports: Inlet and outlet through manifold;
 3-way exhaust through top of valve (3-way only)

Normally-Closed 2- & 3-Way Electronic Poppet Valves with Top Pin Connector




Part No.	Description
ES-2T-□	2-Way Electronic Poppet Valve
ES-3T-□	3-Way Electronic Poppet Valve

Input Pressure: 28" Hg Vac. to 105 psig
 28" Hg Vac. to 50 psig (L)
 28" Hg Vac. to 25 psig (H)

Air Flow: 0.6 scfm @ 100 psig
 0.5 scfm @ 50 psig (L)
 0.45 scfm @ 25 psig (H)

Ports: Inlet and outlet through manifold;
 3-way exhaust through top of valve (3-way only)

Normally-Closed 2- & 3-Way Electronic Poppet Valves with Wire Leads




Part No.	Description
ES-2W-□	2-Way Electronic Poppet Valve
ES-3W-□	3-Way Electronic Poppet Valve

Input Pressure: 28" Hg Vac. to 105 psig
 28" Hg Vac. to 50 psig (L)
 28" Hg Vac. to 25 psig (H)

Air Flow: 0.6 scfm @ 100 psig
 0.5 scfm @ 50 psig (L)
 0.45 scfm @ 25 psig (H)

Ports: Inlet and outlet through manifold;
 3-way exhaust through top of valve (3-way only)

Normally-Closed 2- & 3-Way Electronic Poppet Valves with Board Mount



Part No.	Description
ES-2B-□	2-Way Electronic Poppet Valve
ES-3B-□	3-Way Electronic Poppet Valve

Input Pressure: 28" Hg Vac. to 105 psig
 28" Hg Vac. to 50 psig (L)
 28" Hg Vac. to 25 psig (H)

Air Flow: 0.6 scfm @ 100 psig
 0.5 scfm @ 50 psig (L)
 0.45 scfm @ 25 psig (H)

Ports: Inlet and outlet through manifold;
 3-way exhaust through top of valve (3-way only)

For Cable and Connectors, see [Page 204](#).